

Supplement

Title: 717 Inst.Sht. Supplement Issue: **2**
Part Number: 690013 Issue Date: 9/11
Print Date: March 1998 Page Count: 3
Revision/Date: 2, 3/06

This supplement contains information necessary to ensure the accuracy of the document described above.

Change #1

On the second panel, under ***Symbols***, add the following:

 N10140	Conforms to relative Australian standards
---	---

Change #2 59696,

On the first panel, under “The 717 Pressure Calibrators (hereafter, “the Calibrator”) include” add the following:

- 717 15G
- 717 10000G

On the second panel, under ***Input Units***, add the following:

- inH₂O @ 60 °F

Under the ***Replacement Parts and Accessories***, add the following to the Table:

Item	Parts or Accessory	No.	Qty
⑮	717 15G Top Case Decal	4058885	1
⑯	717 10000G Top Case Decal	4058897	1
⑰	717 15G LCD Bezel	4058851	1
⑱	717 10000G LCD Bezel	4058860	1

Under ***Specifications*** replace the entire section with the following:

Specifications

Specifications apply for ambient temperature from +18 °C to +28 °C unless stated otherwise. "Counts" are the number of increments or decrements of the least significant digit.

Model	Range	Max	Accuracy ^[1]	
			6 month	1 year
717 1G	-1 to 1 psi	5 psi	0.050 %	0.050 %
	-7 to 7 kPa	34.5 kPa		
717 15G	-12 to 15 psi	30 psi	0.025 %	0.035 %
	-83 to 103 kPa	207 kPa		
717 30G	-12 to 30 psi	60 psi	0.025 %	0.035 %
	-83 to 207 kPa	413 kPa		
717 100G	-12 to 100 psi	200 psi	0.025 %	0.035 %
	-83 to 690 kPa	1.4 mPa		
717 300G	-12 to 300 psi	375 PSI	0.035 %	0.050 %
	-83 to 2.1 mPa	2.6 mPa		
717 500G	0 to 500 psi	1000 psi	0.025 %	0.035 %
	0 to 3.4 mPa	6.9 mPa		
717 1000G	0 to 1000 psi	2000 psi	0.025 %	0.035 %
	0 to 6.9 mPa	13.8 mPa		
717 1500G	0 to 1500 psi	3000 PSI	0.025 %	0.035 %
	0 to 10.3 mPa	20.7 mPa		
717 3000G	0 to 3000 psi	6000 PSI	0.025 %	0.035 %

	0 to 20.7 mPa	41.4 mPa		
717 5000G	0 to 5000 psi	10000 PSI	0.025 %	0.035 %
	0 to 34.5 mPa	69 mPa		
717 10000G	0 to 10000 psi	15000 psi	0.035 %	0.050 %
	0 to 69 mPa	103.4 mPa		
[1] In an RF field of 1 V/m to 3 V/m between the frequencies of 1.4 GHz to 2.0 GHz, add 120 counts to specified accuracy.				

Change #3, 59844

In the **Specification** section, add the following:

Specifications apply to the 717 Pressure Calibrators with firmware version 4.0 or greater. To verify the firmware version, press and hold  button and power on the Calibrator.